

MICROTRONIC MICROELECTRONIC VERTRIEBS GMBH

# D & L Automator

Automated system for  
Dip and Look



# Automated & PC Controlled *Dip and Look* automator

## Parameters for dipping:

- Temperature
- Immersion speed
- Immersion depth
- Dwell time
- Withdrawal speed


## Features:

- High precision system
- Repeatable dipping of the specimen
- Easy to use touch screen for settings and operation
- Built in PC with Windows 10
- Durable and reliable
- Tool to automatically measure the bath level
- Tool holder with easy clip funktion
- Easy changeover
- Magnetic fixture for tool holder
- Light Curtain to automatic measure the length of the test coupon
- Designed and made in Bavaria (Germany)

## Standards:

IPC/J-STD-003






Touch panel display



Test area with light curtain and easy to use tool holder



MICROTRONIC MICROELECTRONIC VERTRIEBS GMBH

## The Future in Solderability Test

Microtronics' mindset is creating value for our customers in the industries we are serving. Our deep experience and leadership in core quality control technologies leads us in the development and distribution of cutting-edge equipment.

Through permanent improvement, worldwide support, training and tight cooperation with our customers, we guarantee high quality products and service.

Local representatives are permanently trained to give you the best possible support - worldwide.



Microtronic Microelectronic Vertriebs GmbH  
Kleingrötzing 1  
84494 Neumarkt-Sankt Veit  
Tel: +49 8722 9620-0 - Fax: -30  
[www.microtronic.de](http://www.microtronic.de)  
[lbt210@microtronic.de](mailto:lbt210@microtronic.de)



### Your Local Contact:

S T and S Group  
6019 Atwood Dr., Suite 1  
Richmond, KY, 40475, USA

TEL: 869-353-5914  
[www.standsgroup.com](http://www.standsgroup.com)